KDN480B

Insulated busbar 4P 80A fork 16mm² 56M

Technical properties

Electric current	
Rated current	80 A
Architecture	
Number of poles	4
Dimensions	
Length	1,000 mm
Voltage	
Rated impulse withstand voltage Uimp	4,500 V
Connection	
Cross-section rigid conductor	16 mm²
Connector/plug type	Phase busbar with fork
Capacity	
Number of modules	56