MZ201



Auxiliary contact 1C+1O 6A 240V AC

Technical properties

Electric current	
Rated current	6 A
Connectivity	
Type of connection	Screw terminal
Mounting type	Click mounting
Capacity	
Number of modules	0.50
Connection	
Type of contacts	1NC+1NO
Cross-section flexible conductor	6 mm²
Cross-section rigid conductor	10 mm²
Voltage	
Rated insulation voltage Ui	4,000 V
Type voltage supply	AC
Endurance	
Number of mechanical operations	12,000
Electric endurance in number of cycles	6,000
Use conditions	
Operating temperature	-25 - 60 °C
Storage/transport temperature	-40 - 80 °C
Power	
Total power loss under IN	0.10 W
Dimensions	
Height	80 mm
Width	9.50 mm
Depth	40 mm
Equipment	
Number of INV contacts	0
Number of NC contacts	1