ST309

Safety Transformer 20VA 12V

Technical properties

Voltage	
Output voltage	12 - 12 V
Rated operational voltage Ue	230 - 230 V
Rated insulation voltage Ui	4,000 V

Power	
Power consumption VA	20 VA

Connection	
Cross-section flexible conductor	4 mm²
Cross-section rigid conductor	6 mm²

Frequency	
Frequency	50 - 50 Hz

Installation, mounting	
Mounting on	DIN rail

Use conditions	
Operating temperature	-20 - 35 °C

Capacity	
Number of modules	4

Dimensions	
Height	85 mm
Width	70 mm
Depth	58 mm

Safety	
Ingress Protection (IP) class	IP20
Temperature protection	Yes

Equipment	
Is short-circuit protected	Yes
On/off switch	No