

TGA200



Power supply 24 V DC 1A

Technical properties

Electric current

Output current	1,000 mA

Functions

Output voltage adjusted	Yes

Frequency

Frequency	50 - 60 Hz

Power

Power consumption standby	0.20 W

Capacity

Number of modules	4

Voltage

Output voltage	24 - 24 V

Use conditions

Operating temperature	0 - 45 °C