WXP2502

Plate gallery 1 gang latté

Technical properties

Architecture	
Fixing mode	Clipped

Dimensions	
Depth	9.3 mm
Height	88 mm
Width	92 mm

Capacity	
Number of sockets	1

Materials	
Free area for finishing name	latté
Surface appearance	matt

Installation, mounting	
Mounting way	horizontal

Equipment	
With transparent product label holder	No

Standards	
European directive WEEE	not concerned

Safety	
IK protection code against mecanical impacts	05
RoHS conform	Yes

Use conditions	
Operating temperature	-10…35 °C
Storage/transport temperature	-10…50 °C

Identification	
Range	gallery
Composition	Surface mounted frame