TRM692G

IK04

IP20

Module 1 flush mounted output 3A for shutters or blinds + 2 inputs, KNX radio

Technical characteristics

Architecture

Bus system	KNX
Number of blinds/shutters outputs	1

Controls and indicators

Indicator lamp	yes

Connectivity

Bus system radio frequent	Yes

Main electrical features

Frequency	50 Hz
Type of supply voltage	AC

Power

Contact rating with 230 V in AC1	690 W
Total power loss under IN	450 mW
Power dissipation per coil	150 mW

Connection

Type of connection	with screw
Number of contacts	1
Type of connection	with screw-in lift terminals

Use conditions

Operating temperature	-10…50 °C