VE110L

Enclosure,vector,IP5x,10 Modules,version Austria

Technical characteristics

Connection

Number of conduit inlets	6

Voltage

Nominal voltage	400 - 400 V

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	63 A

Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	No
Has earthing terminal block	No
Has mounting plate	No

Capacity

Number of modules	10

Functions

With conduit inlets	Yes

Dimensions

Height	210 mm
Width	237 mm
Depth	114 mm
Number of width units	10

Cover, door

Number of cabinet doors	1
Number of locks	0
Door/cover is transparent	Yes

Materials

Material	Polystyrene (PS)

RAL code	7035
Colour	Light grey
Ultraviolet-resistant	No

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP65
Locking type	Snap on lock, Without lock
Glow wire test	750 °C