




75161785



Berker S.1/B.3/B.7 Push Button 1-gang, Comfort with Label, Anthracite/Aluminium

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With room temperature controller	No
----------------------------------	----

Function	for switch, push-button, dimmer and shutter functions
----------	-------------------------------------------------------

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--------------------------------------------

Controls and indicators

With LED indication	Yes
---------------------	-----

Number of buttons	1
-------------------	---

Operation	one push-button operation for switching, pushing, shutters and dimming, activation of second user level via object
-----------	--------------------------------------------------------------------------------------------------------------------

Dimensions

Labelling field length (W x H)	52.3 mm
--------------------------------	---------

Height	55.5 mm
--------	---------

Width	55.4 mm
-------	---------

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	-----------------------------------------------------------------------------------------

Screen

With display	No
--------------	----

Materials

Colour of labelling	217,217,217
---------------------	-------------

Colour of design line	aluminium/anthracite
-----------------------	----------------------

Colour independent of design lines	for anthracite and aluminium
------------------------------------	------------------------------

Colour	aluminium/anthracite
--------	----------------------

RAL colour	RAL 7016 - Anthracite grey
------------	----------------------------

Material	thermoplastic
----------	---------------

Material for printing	Paper
-----------------------	-------

Type of surface treatment	untreated
---------------------------	-----------

Material family	Plastic
-----------------	---------

LED control

LED	with white operation LED and 2 red status LEDs
Connection	
Bus coupling unit	for bus coupling unit flush-mounted
Settings	
Parameterisation	single and two push-button operation parameterisable
Scope of delivery	
Bus connection included	No
Equipment	
Number of actuation points	2
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 1gang
Use	
Differentiation characteristic 1 - Sales	with labelling field
Differentiation characteristic 3 - Sales	with horizontal operation
Safety	
Protection index IP	IP20
Protection	with dismantling protection
Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte
Use conditions	
Operating temperature	-5...45 °C
Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Secondary design line(s)	KNX, Berker S.1, Berker B.3, Berker B.7