


75663775



## Push-button 3gang with room thermostat, display, K.1, anthracite

### Technical properties

#### Functions

With room temperature controller	Yes
Function	for switch, push-button, dimmer, blind and thermostat functions ; with valve protection function
Timers	with room temperature timer
Operating mode	controller operating modes: comfort, standby, night and frost/heat protection mode

#### Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

#### Controls and indicators

With LED indication	Yes
Dimming	area dimming
Number of buttons	3
Operation	one push-button operation for switching, pushing, shutters and dimming ; blind operating concepts short-long-short and long-short parameterisable
Indication / display	display of operating mode, controller lockout, room/outside temperature, time (clock required) ; LC display with symbol display
Button / push-button	with 2 additional display buttons

#### Connectivity

Encoding	with button blocking function
----------	-------------------------------

#### Dimensions

Labelling field length (W x H)	66.8 x 24.9 mm
Height	111.1 mm
Width	70.9 mm

#### Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

#### Screen

With display	Yes
--------------	-----

#### Materials

Colour of labelling	217,217,217
Colour of design line	anthracite
Material for printing	Paper
Surface appearance	glossy

**LED control**

LED	with white operation LED and 6 red status LEDs
-----	--

**Connection**

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

**Settings**

Parameterisation	single and two push-button operation parameterisable ; end customer display scope parameterisable ; presence button parameterisable to extend comfort
Programming	programmable from ETS2, V1.2a

**Scope of delivery**

Bus connection included	No
-------------------------	----

**Equipment**

Number of actuation points	8
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 3gang
Heating	for heating and/or cooling mode with/without auxiliary step
Control	for individual single room temperature control ; control parameter for heating / cooling unit pre-set ; for continuous (PI) or switched (2-point) control of max. 2 control circuits

**Use**

Differentiation characteristic 1 - Sales	Labelling fields
Differentiation characteristic 2 - Sales	Display

**Software**

Update	with flash-controller technology
--------	----------------------------------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection
Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte

**Use conditions**

Operating temperature	-5...45 °C
Temperature	temperature measurement via internal and/or external sensor with mean value formation
Energy efficiency class	IV (2%)

**Identification**

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker K.1/K.5

**Instructions**

---

Special note text

Use only in combination with frame frame with large cut-out.