



47487109

SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,K1

Technical characteristics

Architecture

| | |
|-------------|------------------------|
| Design | according to DIN 49440 |
| Fixing mode | flush-mounting |

Configuration

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Rated voltage | 250 V AC |
| Frequency | 50/60 Hz |
| Rated current | 16 A |

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Dimensions

| | |
|-----------------|-------|
| Insertion depth | 32 mm |
|-----------------|-------|

Cover, door

| | |
|---------------|---|
| Hinged covers | when opening hinged cover, it can be arrested in end position |
| Cover | Central cover plate |

Materials

| | |
|-----------------------|-----------------------|
| Colour of design line | polar white |
| Colour | polarwhite |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Material | thermoplastic |

Installation, mounting

| | |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

Connection

| | |
|----------------------|--------------------------|
| Connection terminals | according to IEC 60884-1 |
| Connection terminals | according to VDE 0620-1 |
| Type of connection | with plug-in terminals |

Use

| | |
|--|-----------------|
| Differentiation characteristic 1 - Sales | Labelling field |
|--|-----------------|

| | |
|--|-----------------------------|
| Differentiation characteristic 2 - Sales | enhanced contact protection |
|--|-----------------------------|

| | |
|--|--|
| Differentiation characteristic 3 - Sales | Mounting orientation variable in 45° steps |
|--|--|

Safety

| | |
|---|----|
| IK protection code against mechanical impacts | 05 |
|---|----|

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

| | |
|------------|--|
| Protection | enhanced contact protection VDE 0620-1 |
|------------|--|

| | |
|----------------------------------|-----|
| With enhanced contact protection | Yes |
|----------------------------------|-----|

Identification

| | |
|------------------|------------|
| Main design line | Berker K.1 |
|------------------|------------|

Instructions

| | |
|------------------|--|
| Information text | Labelling field height arranged for 6 mm P-touch strips. Specially suited to combinations of several socket outlets if right angle plugs are used. |
|------------------|--|