

75142930

KNX glass sensor 2gang comf, intg bus coupl. unit, KNX-TS sensor, glass p.white



More Information

Test and administrative marks, WEEE_SYMBOL.JPG trademarks, brands

Test and administrative marks, INSTALLATEUR__ADMIN-SYMBOL.JPG trademarks, brands

Test and administrative marks, EAC-LOGO__ADMIN-SYMBOL.EPS trademarks, brands

Bus connection included Yes

Inscribable, with labelling field No

RAL colour RAL 9010 - Pure white

Colour of design line glass polar white

Colour glass polar white

Surface appearance glossy;matt

Current consumption 12.5 mA

Depth 37.7 mm

Depth	5.7 mm
Designation syntax: Core designation/function	Glass sensor
Product description	KNX Glass sensor 2gang comfort
Designation syntax: System / brand	KNX
Designation syntax: variant	2gang comfort
Designation syntax: differentiation feature	integrated bus coupling unit 3
Differentiation characteristic 3 - Sales	with integral bus coupling unit
Differentiation symbol 3	INTEGRIERTER-BUSANKOPPLER__DIFF-SYMBOL.EPS
Dimensions (W x H x D)	86/160/5.7 mm
Height	160 mm
	Many options for labelling (text and/or symbols) are available via the web configurator at www.hager.de .
Note Configurator	Caution! For individually labelled glass and touch sensors (configured variations), the new web configurator generates a layout number, which must be additionally specified when placing the order.
Information text	Only suitable for KNX.
Material	glass
Product type	Glas-sensor
Fixing mode	flush-mounting
Number of actuation points	4
Number of buttons	0
Operating temperature	-5/45 °C
Operating voltage	21 ... 32 V DC
Protection classes/types	IP20__PROTECTION-SYMBOL.EPS
Secondary design line(s)	KNX ; Berker TS Sensor
S-number	28 035 87
Supplier	FELA
Search words	Push-button;Push-button comfort, with labelling field
type of base (dado trunking)	shining
Colour	polarwhite
Type of surface treatment	Tampography

Application, usage	KNX - operating systems
Bus connection	bus connection via connecting terminal
Bus coupling unit	with integral bus coupling unit
Extension unit	extension unit for light scene push-button
Function	for switch, push-button, dimmer and shutter functions ; Blocking function for sensor surface e.g. for cleaning the glass surface
Installation mode	for vertical mounting
LED	with blue operation LED and 4 white status LEDs
Matching products	for glass frames in the same "style" for additional applications, see the Design line B.7 ; for additional products to complement the installation in matching colours ; materials, refer to the Design platform S.1 ; B.x
Operation	operation by gently touching the sensor surfaces on the white LED
Temperature	temperature measurement via internal temperature sensor or external communication object ; integrated temperature sensor for operation as controller extension unit ; additional connection for external temperature sensor
Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
Width	86 mm
With anti-theft/dismantling protection	Yes
With display	No
With IR sensor	No
With LED indication	Yes
With room temperature controller	Yes
Unit	PCE
EAN	4011334383833
Sales status	3C