



ADC240T

RCBO 1M 1P 6kA C-40A 30mA A Class

Technical properties

Architecture

Type of pole	1P
Curve	C

Electric current

Rated current	40 A
Rated residual operating current I_{dn}	30 mA
Rated current -25°C	48,66 A
Rated current at -20°C	47,88 A
Rated current -15°C	47,09 A
Rated current -10°C	46,30 A
Rated current -5°C	45,51 A
Rated current at 0°C	44,73 A
Rated current 5°C	43,94 A
Rated current 10°C	43,15 A
Rated current 15°C	42,36 A
Rated current at 20°C	41,58 A
Rated current 25°C	40,79 A
Rated current 30°C	40 A
Rated current 35°C	39,15 A
Rated current at 40°C	38,30 A
Rated current at 50°C	36,60 A
Rated current 55°C	35,75 A
Rated current 60°C	34,90 A
Min./max. threshold value of the AC thermal operation	1,13 - 1,45 A

Safety

Residual current type	A
Ingress Protection (IP) class	IP20

Main electrical attributes

Rated short-circuit breaking capacity I_{cn} AC according to IEC 60898-1	6 kA
--	------

Voltage

Rated insulation voltage U_i	250 V
Rated impulse withstand voltage U_{imp}	4000 V
Rated operational voltage U_e	230 - 240 V

Overvoltage category according to IEC 60947-1	3
Power	
Total power loss under IN	12,50 W
Frequency	
Frequency	50 - 60 Hz
Use conditions	
Max. Altitude	2000 m
Class of energy limitation I ² t	3
Operating temperature	-5 - 40 °C
Storage/transport temperature	-40 - 70 °C
Endurance	
Electric endurance in number of cycles	2000
Number of mechanical operations	10000
Connection	
Cross-section of input with screws, for flexible conductors	1 - 10 mm ²
Cross-section of input with screws, for massive conductors	1 - 16 mm ²
Cross-section of input and output with screws, for flexible conductors	1 - 16 mm ²
Cross-section of input and output with screws, for massive conductors	1 - 25 mm ²
Installation, mounting	
Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect
Capacity	
Number of modules	1
Dimensions	
Height	115 mm
Width	17,80 mm
Depth	70 mm
Compatibility	
Suitable for DIN Rail	Yes