



ADC216B

RCBO 1M 1P 10kA C-16A 30mA A

Technical properties

Architecture

Type of pole	1P
Curve	C

Electric current

Rated current	16 A
Rated residual operating current $I_{\Delta n}$	30 mA
Rated current -25°C	20,81 A
Rated current at -20°C	20,38 A
Rated current -15°C	19,94 A
Rated current -10°C	19,50 A
Rated current -5°C	19,06 A
Rated current at 0°C	18,63 A
Rated current 5°C	18,19 A
Rated current 10°C	17,75 A
Rated current 15°C	17,31 A
Rated current at 20°C	16,88 A
Rated current 25°C	16,44 A
Rated current 30°C	16 A
Rated current 35°C	15,70 A
Rated current at 40°C	15,40 A
Rated current at 50°C	14,80 A
Rated current 55°C	14,50 A
Rated current 60°C	14,20 A
Min./max. threshold value of the AC thermal operation	1,13 - 1,45 A

Safety

Residual current type	A
Ingress Protection (IP) class	IP20

Main electrical attributes

Rated short-circuit breaking capacity I_{cn} AC according to IEC 60898-1	10 kA
--	-------

Voltage

Rated insulation voltage U_i	250 V
Rated impulse withstand voltage U_{imp}	4000 V
Rated operational voltage U_e	230 - 240 V

Overvoltage category according to IEC 60947-1	3
Power	
Total power loss under IN	4,90 W
Frequency	
Frequency	50 - 60 Hz
Use conditions	
Max. Altitude	2000 m
Class of energy limitation I ² t	3
Operating temperature	-5 - 40 °C
Storage/transport temperature	-40 - 70 °C
Endurance	
Electric endurance in number of cycles	2000
Number of mechanical operations	10000
Connection	
Cross-section of input with screws, for flexible conductors	1 - 10 mm ²
Cross-section of input with screws, for massive conductors	1 - 16 mm ²
Cross-section of input and output with screws, for flexible conductors	1 - 16 mm ²
Cross-section of input and output with screws, for massive conductors	1 - 25 mm ²
Installation, mounting	
Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect
Capacity	
Number of modules	1
Dimensions	
Height	115 mm
Width	17,80 mm
Depth	70 mm
Compatibility	
Suitable for DIN Rail	Yes