



AEA932T

RCBO 1P+N 6kA C-32A 100mA A

Technical properties

Architecture

Type of pole	1P+N
Curve	C

Electric current

Rated current	32 A
Rated residual operating current I _{dn}	100 mA
Rated current -25°C	38,30 A
Rated current at -20°C	37,80 A
Rated current -15°C	37,20 A
Rated current -10°C	36,70 A
Rated current -5°C	36,10 A
Rated current at 0°C	35,60 A
Rated current 5°C	35 A
Rated current 10°C	34,40 A
Rated current 15°C	33,80 A
Rated current at 20°C	33,20 A
Rated current 25°C	32,60 A
Rated current 30°C	32 A
Rated current 35°C	31,50 A
Rated current at 40°C	31 A
Rated current at 50°C	30 A
Rated current 55°C	29,50 A
Rated current 60°C	29 A
Correction factor of rating current for 2 devices placed side by side	1
Correction factor of rating current for 3 devices placed side by side	0,95
Correction factor of rating current for 4 and 5 devices placed side by side	0,90
Correction factor of rating current for 6 devices placed side by side	0,85
Min./max. threshold value of the AC thermal operation	1,13 - 1,45 A

Safety

Residual current type	A
Ingress Protection (IP) class	IP20

Main electrical attributes

Rated short-circuit breaking capacity I_{cn} AC
according to IEC 60898-1

6 kA

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Voltage

Rated insulation voltage U _i	500 V
Rated impulse withstand voltage U _{imp}	4000 V
Max. operating voltage	240 V
Rated operational voltage U _e	230 - 240 V
Overvoltage category according to IEC 60947-1	3

Power

Total power loss under I _N	7,60 W
---------------------------------------	--------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Use conditions

Max. Altitude	2000 m
Class of energy limitation I ² t	3
Operating temperature	-25 - 40 °C
Storage/transport temperature	-25 - 70 °C

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	4000

Connection

Cross-section flexible conductor	1 - 16 mm ²
Cross-section rigid conductor	1 - 25 mm ²
Cross-section of input with screws, for flexible conductors	1 - 16 mm ²
Cross-section of input with screws, for massive conductors	1 - 25 mm ²
Cross-section of input and output with screws, for flexible conductors	1 - 16 mm ²
Cross-section of input and output with screws, for massive conductors	1 - 25 mm ²

Installation, mounting

Nominal tightening torque	2,10 - 2,10 Nm
Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect

Capacity

Number of modules	2
-------------------	---

Dimensions

Height	83 mm
--------	-------

Width	35 mm
Depth	68 mm
Compatibility	
Suitable for DIN Rail	Yes