



CDF540T

**RCCB 1P+N 40A 30mA F**

**Technical properties**

**Architecture**

Type of pole	1P+N
--------------	------

**Electric current**

Rated current	40 A
Rated residual operating current $I_{\Delta n}$	30 mA
Breaking and opening capacity $I_{dm}$	1,25 kA
Rated conditional short-circuit current $I_{nc}$ according to EN61008-1	10 kA
Rated current -25°C	40 A
Rated current at -20°C	40 A
Rated current -15°C	40 A
Rated current -10°C	40 A
Rated current -5°C	40 A
Rated current at 0°C	40 A
Rated current 5°C	40 A
Rated current 10°C	40 A
Rated current 15°C	40 A
Rated current at 20°C	40 A
Rated current 25°C	40 A
Rated current 30°C	40 A
Rated current 35°C	40 A
Rated current at 40°C	40 A
Rated current at 45°C	40 A
Rated current at 50°C	40 A
Rated current 55°C	40 A
Rated current 60°C	40 A
Rated current 65°C	40 A
Rated current 70°C	40 A

**Installation, mounting**

Nominal tightening torque top terminal	3,60 - 3,60 Nm
Nominal tightening torque down terminal	3,60 - 3,60 Nm
Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect, Bypass

**Voltage**

Rated operational voltage $U_e$	240 - 240 V
---------------------------------	-------------

Type voltage supply	AC
Rated insulation voltage Ui	500 V
Dielectric strength value of power frequency	2 kV
Rated impulse withstand voltage Uimp	4000 V
Rated impulse withstand voltage Uimp IEC 60947-3	6000 V
Max. operating voltage	253 V
<b>Frequency</b>	
Frequency	50 - 50 Hz
<b>Capacity</b>	
Number of modules	2
<b>Compatibility</b>	
Suitable for DIN Rail	Yes
<b>Safety</b>	
Residual current type	F
Ingress Protection (IP) class	IP20
<b>Connection</b>	
Cross-section of output with screws, for massive conductors	1 - 25 mm²
Cross-section of output with screws, for flexible conductors	1 - 16 mm²
<b>Power</b>	
Total power loss under IN	3,31 W
<b>Use conditions</b>	
Max. Altitude	2000 m
Operating temperature	-25 - 70 °C
<b>Endurance</b>	
Electric endurance in number of cycles	10000
Number of mechanical operations	20000
<b>Connectivity</b>	
Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal
<b>Dimensions</b>	
Height	85 mm
Width	36 mm
Depth	70 mm