



CDA440T

**RCCB 4P 40A 30mA A Class**

**Technical properties**

**Architecture**

Type of pole	3P+N
--------------	------

**Electric current**

Rated current	40 A
Rated residual operating current I <sub>dn</sub>	30 mA
Breaking and opening capacity I <sub>dm</sub>	1,50 kA
Rated conditional short-circuit current I <sub>nc</sub> according to EN61008-1	6 kA
Rated current -25°C	40 A
Rated current at -20°C	40 A
Rated current -15°C	40 A
Rated current -10°C	40 A
Rated current -5°C	40 A
Rated current at 0°C	40 A
Rated current 5°C	40 A
Rated current 10°C	40 A
Rated current 15°C	40 A
Rated current at 20°C	40 A
Rated current 25°C	40 A
Rated current 30°C	40 A
Rated current 35°C	40 A
Rated current at 40°C	40 A
Rated current at 45°C	40 A
Rated current at 50°C	40 A
Rated current 55°C	40 A
Rated current 60°C	40 A
Rated current 65°C	40 A
Rated current 70°C	40 A

**Main electrical attributes**

Nominal tightening torque top terminal	2,80 - 2,80 Nm
Nominal tightening torque down terminal	2,80 - 2,80 Nm

**Voltage**

Rated operational voltage U <sub>e</sub>	230 - 400 V
Type voltage supply	AC
Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	4000 V

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Capacity**

Number of modules	4
-------------------	---

**Compatibility**

Suitable for DIN Rail	Yes
-----------------------	-----

**Safety**

Residual current type	A
-----------------------	---

Ingress Protection (IP) class	IP20
-------------------------------	------

**Installation, mounting**

Type of top connection for modular devices	Screw terminal
--	----------------

Type of bottom connection for modular devices	biconnect
---	-----------

Nominal tightening torque	2,80 - 2,80 Nm
---------------------------	----------------

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 25 mm <sup>2</sup>
---	------------------------

Cross-section of input and output with screws, for flexible conductors	1 - 16 mm <sup>2</sup>
--	------------------------

**Power**

Total power loss under IN	6,50 W
---------------------------	--------

**Use conditions**

Altitude	2000 m
----------	--------

**Endurance**

Electric endurance in number of cycles	2000
--	------

Number of mechanical operations	4000
---------------------------------	------

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

Top connection alignment for modular devices	Aligned terminal
--	------------------

Down connection alignment for modular devices	Aligned terminal
---	------------------

**Dimensions**

Height	83 mm
--------	-------

Width	70 mm
-------	-------

Depth	70 mm
-------	-------