



CZ001

Auxiliary contact for RCCB 2(1C+1O) 6A 240V AC

Technical properties

Architecture

Fixing mode Clipped

Configuration

Number of modules 1

Main electrical features

Rated operational voltage U_e 230 / 440 V

Frequency 50 Hz

Voltage

Rated insulation voltage 500 V

Rated operational voltage in DC 12 / 250 V

Electric current

Acceptable current rating with AC1 6 A

Rated current 6 A

$I_{min} = f(U = 230 \text{ V AC})$ 6 A

$I_{min} = f(U = 230 \text{ V DC})$ 0.6 A

$I_{min}=f(U=400\text{V AC})$ for power circuit 3 A

Dimensions

Width of installed product 18 mm

Power

Total power loss under I_N 0.1 W

Endurance

Electric endurance in number of cycles 6000

Number of mechanical operations 12000

Installation, mounting

Factory fitted No

Equipment

Quantity of NC contacts 1

Quantity of NO contacts 1

Quantity of INV contacts 0

Standards

European directive WEEE concerned

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -25...60 °C |
| Storage/transport temperature | -40...80 °C |
