



ECP300C

3 Phase kWhmeter via CT 1A or 5A 4M S0 MID

Technical properties

Architecture

Number of poles	4 P
Type of pole	3P+N
Fixing mode	DIN rail type O (symmetrical)

Functions

Precision class	B
Tarif type	T1...T2 (230 V AC) / -

Configuration

Number of modules	4
-------------------	---

Compatibility

Suitable for	Purchase / supply
--------------	-------------------

Main electrical features

Rated operational voltage Ue	92 / 480 V
Type of supply voltage	AC
Frequency	50 Hz

Voltage

Max operating voltage	300 V
Rated impulse withstand voltage	6 kV

Electric current

Minimum operating current	0.001 A
Operating current	0.001 / 6 A
Rated current	5 A
Reference current	1 A
Max. measurement circuit current	6 A

Dimensions

Depth of installed product	60 mm
Height of installed product	90 mm
Width of installed product	72 mm

Power

Power consumed	2 VA
Total power loss under IN	0.6 W
Plage Impulsion/KWh	1 / 10000 Imp/kWh

Electrical specifications

Type of pulse generator	électrical
-------------------------	------------

Measurement

Frequency measuring range	45 to 65 Hz
---------------------------	-------------

Type of measuring instrument	electronical
------------------------------	--------------

Principle of measurement	Measurement transformer
--------------------------	-------------------------

Power supply

Supply voltage	400 V ± 20%
----------------	-------------

Installation, mounting

Tightening torque	0.5Nm
-------------------	-------

Mounting type	din-Rail
---------------	----------

Settings

Value of a pulse	100 Wh
------------------	--------

Transformer interpretation adjustable	1
---------------------------------------	---

Equipment

Type of display	retro illuminated display
-----------------	---------------------------

Tariff model of kilowatt-hour meter	Externa
-------------------------------------	---------

Type of counter	three-phase counter with torus of measurement and impulses output
-----------------	---

Use

Pulse duration	30 / 100 ms
----------------	-------------

Transformation Ratio	50;5 ; 100;5 ; 200;5 ; 250;5 ; 300;5 ; 400;5 ; 600;5 ; 800;5 ; 1000;5 ; 1250;5 ; 1500;5
----------------------	--

Standards

Standard text	EN 50470-1 / 3 ; IEC 62053-21 / 23 ; IEC 61557-12
---------------	---

Certified product	MID (Measuring Instruments Directive)
-------------------	---------------------------------------

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Protection class	isol.class II
------------------	---------------

Use conditions

Operating temperature	-25...55 °C
-----------------------	-------------

Degree of pollution according to IEC 60664 / IEC 60947-2	2
---	---

Altitude	2000 m
----------	--------

Storage/transport temperature	-25...70 °C
-------------------------------	-------------