



ECN140D



1 Phase kWhmeter direct 40A 1M

Technical properties

Architecture

Number of poles	2 P
Type of pole	1P+N

Functions

Precision class	B
Tarif type	One-tariff

Configuration

Number of modules	1
-------------------	---

Compatibility

Suitable for	Purchase
--------------	----------

Main electrical features

Rated operational voltage Ue	184 / 276 V
Type of supply voltage	AC
Frequency	50 Hz

Voltage

Max operating voltage	300 V
Rated impulse withstand voltage	6 kV

Electric current

Minimum operating current	0.02 A
Operating current	0.02 / 40 A
Rated current	40 A
Reference current	5 A
Max. measurement circuit current	40 A

Dimensions

Depth of installed product	58 mm
Height of installed product	92 mm
Width of installed product	18 mm

Power

Power consumed	2 VA
Total power loss under IN	1 W

Electrical specifications

Type of pulse generator	optical
-------------------------	---------

Measurement

Frequency measuring range	45 to 65 Hz
Type of measuring instrument	electronical
Principle of measurement	Direct measurement

Power supply

Supply voltage	230 V \pm 20%
----------------	-----------------

Installation, mounting

Tightening torque	1Nm
Mounting type	din-Rail

Connection

Wire cross section of metering entrance wire	16 mm ²
Wire cross section of metering outgoing wire	16 mm ²

Equipment

Type of display	LCD
Type of counter	single-phase counter

Standards

Standard text	IEC 62053-21 / 23 ; IEC 61557-12
---------------	----------------------------------

Safety

Protection class	isol.class II
Halogen free	No

Use conditions

Operating temperature	-25...55 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Altitude	2000 m
Storage/transport temperature	-25...70 °C