



EE600



IP55

## LED Floodlight with PIR 220 / 360° , white

### Technical properties

#### Architecture

Fixing mode other

#### Functions

Operating mode with test mode

#### Main electrical features

Frequency 50/60 Hz

#### Voltage

Operating voltage 230 V AC

Operating voltage 230 V~ +10%/-15%

#### Power

Halogen switching capacity 230V 410 W

Incandescent bulb power 300 W

#### Endurance

Service life of the LED ≈ 7300 h

#### Detection

Detection angle, settable 220...360 °

Detection field Ø, on floor ≈ 24 m

Frontal detecting distance 12 m

Side detecting distance 12 m

#### Materials

Colour white

RAL colour RAL 9010 - Pure white

#### Lighting control

Brightness measurement range 5 / 1000 Lux

Lumen 3400 lm

#### LED control

Power LED 60 W

#### Incandescent bulbs control

230 V incandescent lamps 300 W

#### Installation, mounting

Maximum Mounting Height 4 m

**Connection**

---

Connection type	1 to 1,5 mm <sup>2</sup>
-----------------	--------------------------

**Settings**

---

Response value sensitivity adjustable	Yes
---------------------------------------	-----

**Equipment**

---

Slewing	LED spotlight horizontally adjustable 180° ; LED spotlight vertically adjustable 340°
---------	--

**Safety**

---

Protection class	isol.class II
------------------	---------------

**Use conditions**

---

Operating temperature	-20...40 °C
-----------------------	-------------

---

Storage/transport temperature	-20...60 °C
-------------------------------	-------------

**Identification**

---

Application, usage	Motion detector
--------------------	-----------------

---

Main design line	Motion detectors
------------------	------------------