



ECP140D

1 Phase kWhmeter direct 40A 1M S0 MID

Technical properties

Architecture

Number of poles	2 P
Fixing mode	DIN rail type O (symmetrical)

Functions

Tarif type	One-tariff
------------	------------

Configuration

Number of modules	1
-------------------	---

Compatibility

Suitable for	Purchase / supply
--------------	-------------------

Main electrical features

Rated operational voltage Ue	92 / 276 V
Type of supply voltage	AC
Frequency	50 Hz

Voltage

Max operating voltage	300 V
Rated impulse withstand voltage	6 kV

Electric current

Minimum operating current	0.02 A
Operating current	0.02 / 40 A
Rated current	40 A
Reference current	5 A
Max. measurement circuit current	40 A

Dimensions

Depth of installed product	60 mm
Height of installed product	92 mm
Width of installed product	18 mm

Power

Power consumed	2 VA
Total power loss under IN	1 W
Plage Impulsion/KWh	1000 Imp/kWh

Electrical specifications

Type of pulse generator	électrical
-------------------------	------------

Measurement

Frequency measuring range	45 to 65 Hz
Type of measuring instrument	electronical
Principle of measurement	Direct measurement

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Wire cross section of metering entrance wire	16 mm ²
Wire cross section of metering outgoing wire	16 mm ²

Settings

Value of a pulse	100 Wh
------------------	--------

Equipment

Type of display	LCD
Type of counter	single-phase counter

Use

Pulse duration	100 ms
----------------	--------

Standards

Standard text	EN 50470-1 / 3 ; IEC 62053-21 / 23 ; IEC 61557-12
European directive WEEE	concerned

Safety

Protection index IP	IP20
Protection class	isol.class II

Use conditions

Operating temperature	-25...55 °C
Altitude	2000 m
Storage/transport temperature	-25...70 °C