



EE610



LED deco lamp with IR detector, white

Technical properties

Architecture

Fixing mode	Screwed
-------------	---------

Functions

Operating mode	with test mode
----------------	----------------

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Operating voltage	230 V AC
-------------------	----------

Dimensions

Installation height	max. 4 m
Recommended installation height	2 m

Power

Halogen switching capacity 230V	175 W
Incandescent bulb power	60 W

Measurement

Detection field, semi-oval shaped	≈ 10 x 12 m
-----------------------------------	-------------

Reach distance

Range, frontal	≈ 12 m
----------------	--------

Detection

Detection angle	140 °
Detection angle	140 °
Frontal detecting distance	12 m
Side detecting distance	6 m

Materials

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Lighting control

Response brightness, adjustable	≈ 5...1000 lx
Brightness measurement range	5 / 1000 Lux
Lumen	1100 lm

LED control

Power LED	15 W
-----------	------

Incandescent bulbs control

230 V incandescent lamps	60 W
--------------------------	------

Installation, mounting

Maximum Mounting Height	4 m
-------------------------	-----

Installation mode	for screw fastening, with dismantling protection
-------------------	--

Connection

Conductor cross-section	1.5...2.5 mm ²
-------------------------	---------------------------

Type of connection	with screw terminals
--------------------	----------------------

Cable

Wire	with cable entry
------	------------------

Settings

Response value sensitivity adjustable	Yes
---------------------------------------	-----

Delay time, adjustable	5 s...15 mn
------------------------	-------------

Scope of delivery

Component	with fitting material
-----------	-----------------------

Safety

Protection class	isol.class II
------------------	---------------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-25...50 °C
-----------------------	-------------

Storage/transport temperature	-30...70 °C
-------------------------------	-------------

Identification

Application, usage	Motion detector
--------------------	-----------------

Main design line	Motion detectors
------------------	------------------