



EGN200AU

Multi-function time switch 2 channels bluetooth

Technical properties

Voltage

Nominal voltage	230 - 240 V
-----------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

230 V incandescent and halogen lamp	2300 W
-------------------------------------	--------

Lighting

Max. load fluorescent lamp in series	1000 W
--------------------------------------	--------

Functions

Power reserve in years	10 y
------------------------	------

With network synchronisation	No
------------------------------	----

With quartz synchronisation	Yes
-----------------------------	-----

Equipment

Accuracy per day	0,25 s
------------------	--------

With impulse programme	Yes
------------------------	-----

Number of channels	2
--------------------	---

Connection

Type of contacts	1x changeover
------------------	---------------

Cross-section flexible conductor	0.2 - 2.5 mm ²
----------------------------------	---------------------------

Cross-section rigid conductor	0.2 - 4 mm ²
-------------------------------	-------------------------

Settings

Daily programme	Yes
-----------------	-----

Weekly programme	Yes
------------------	-----

Annual programme	Yes
------------------	-----

Use conditions

Operating temperature	-5 - +45 °C
-----------------------	-------------

Texts

Type of connection	With screw terminal
--------------------	---------------------

Dimensions

Height	90 mm
--------	-------

Width	35,80 mm
-------	----------

