



EG071



IP20

Weekly time switch 1 channel, 1 module

Technical properties

Functions

Number of function channels	1
-----------------------------	---

Configuration

Number of modules	1
-------------------	---

Controls and indicators

Indication / display	LC display
----------------------	------------

Main electrical features

Rated operational voltage U _e	230 V
Frequency	50 Hz

Voltage

Operating voltage	230 V~
-------------------	--------

Dimensions

Depth of installed product	64 mm
Height of installed product	92 mm
Width of installed product	18 mm
Width of rail mounted device (RMD)	1 modules

Power

Power consumed	1 VA
Total power loss under IN	1 W
Loss power at full load	≈ 1 W
Power dissipation per coil	1 W

Measurement

Running accuracy	± 1 s/day
------------------	-----------

Battery

Power reserve [years]	≈ 3 a
Battery / storage battery	with lithium coin cell battery type: CR1632
Charging time of the power reserve in hours	0

Incandescent bulbs control

Max. power with incandescent lamps	1000 W
230 V incandescent lamps and halogen lamps	max. 1000 W

Installation, mounting

Mounting type	din-Rail
Installation mode	for mounting on DIN rail
Connection	
Connection cross-sect. flexible conductor	1 / 4mm ²
Connection cross-sect. rigid cable	1 / 4mm ²
Conductor cross-section (flexible)	1...4 mm ²
Conductor cross-section (rigid)	1...4 mm ²
Number of contacts	1
Type of contacts	1 changeover
Contact	with potential-free switching contact
Settings	
Number of program steps	20
Summer / Winter time change	manual
Shortest switching time	1 mn
Type of programming	digital
Program cycles	Programme cycles: 1 x 7 days
Programming cycle	1X7D.
Equipment	
Number of channels	1
Number of switching times for on/off	20
Supply failure reserve	3 years
With holidays program	No
Use	
Cycle	weekly
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	-10...50 °C
Working accuracy	1
Storage/transport temperature	-10...60 °C