



EH010



## Daily time switch 1 channel, 16A, 1 module

### Technical properties

#### Equipment

Number of channels	1
--------------------	---

#### Frequency

Frequency	50 - 50 Hz
-----------	------------

#### Power

Power consumption during operation	0,50 VA
230 V incandescent and halogen lamp	900 W
Power loss at full load	1 W

#### Functions

Number of function channels	1
-----------------------------	---

#### Connection

Number of contacts	1
Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 10 mm <sup>2</sup>

#### Use conditions

Operating temperature	-10 - 55 °C
-----------------------	-------------

#### Capacity

Number of modules	1
-------------------	---

#### Dimensions

Height	80 mm
Width	18 mm
Depth	60 mm

#### Texts

Switch mode	NO contact
Installation mode	For mounting on DIN rail
Type of connection	With screw terminals

#### Electric current

Max. power (cos phi 0,6)	3 A
--------------------------	-----

#### Endurance

Electrical durability at nominal load in AC1 in operating cycles	30000
---	-------

**Voltage**

---

Rated operational voltage  $U_e$

210 - 230 V