



EGN103



1 channel digital time switch weekly cycle

Technical properties

Voltage

Nominal voltage 230 - 230 V

Frequency

Frequency 50 - 60 Hz

Power

230 V incandescent and halogen lamp 2300 W

Lighting

Max. load fluorescent lamp in series 1000 W

Functions

Power reserve in years 5 y

With network synchronisation No

With quartz synchronisation Yes

Equipment

Accuracy per day 1,50 s

With impulse programme No

Number of channels 1

Connection

Type of contacts 1x changeover

Cross-section flexible conductor 1 - 6 mm²

Cross-section rigid conductor 1.5 - 10 mm²

Settings

Daily programme Yes

Weekly programme Yes

Annual programme No

Use conditions

Operating temperature -5 - +45 °C

Texts

Type of connection With screw terminal

Dimensions

Height 85 mm

Width 35,80 mm

