



EH110



Daily time switch 1 channel, analog, 3 modules

Technical properties

Equipment

Number of channels	1
--------------------	---

Frequency

Frequency	50 - 50 Hz
-----------	------------

Power

Power consumption during operation	0,50 VA
------------------------------------	---------

230 V incandescent and halogen lamp	900 W
-------------------------------------	-------

Power loss at full load	1 W
-------------------------	-----

Functions

Number of function channels	1
-----------------------------	---

Connection

Number of contacts	1
--------------------	---

Cross-section flexible conductor	1 - 4 mm ²
----------------------------------	-----------------------

Cross-section rigid conductor	1 - 4 mm ²
-------------------------------	-----------------------

Use conditions

Operating temperature	-10 - 45 °C
-----------------------	-------------

Capacity

Number of modules	3
-------------------	---

Dimensions

Height	90 mm
--------	-------

Width	65 mm
-------	-------

Depth	54 mm
-------	-------

Texts

Switch mode	Change-over contact, usable as NC or NO
-------------	---

Installation mode	For mounting on DIN rail
-------------------	--------------------------

Type of connection	With screw terminals
--------------------	----------------------

Electric current

Max. power (cos phi 0,6)	3 A
--------------------------	-----

Switching current	16 A
-------------------	------

Endurance

Electrical durability at nominal load in AC1 in operating cycles	50000
--	-------

Voltage

Rated operational voltage Ue

230 - 230 V