



EHN010



Daily time switch 1 channel, 1 module

Technical properties

Equipment

| | |
|--------------------|---|
| Number of channels | 1 |
|--------------------|---|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Power

| | |
|-------------------------------------|-------|
| Power consumption during operation | 1 W |
| 230 V incandescent and halogen lamp | 900 W |
| Power loss at full load | 1 W |

Functions

| | |
|-----------------------------|---|
| Number of function channels | 1 |
|-----------------------------|---|

Connection

| | |
|----------------------------------|-----------------------|
| Number of contacts | 1 |
| Cross-section flexible conductor | 1 - 6 mm ² |
| Cross-section rigid conductor | 1 - 6 mm ² |

Use conditions

| | |
|-----------------------|--------------|
| Operating temperature | -20 - +50 °C |
|-----------------------|--------------|

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Dimensions

| | |
|--------|---------|
| Height | 90 mm |
| Width | 17,5 mm |
| Depth | 60 mm |

Texts

| | |
|--------------------|--------------------------|
| Switch mode | NO contact |
| Installation mode | For mounting on DIN rail |
| Type of connection | With screw terminals |

Electric current

| | |
|--------------------------|-----|
| Max. power (cos phi 0,6) | 3 A |
|--------------------------|-----|

Endurance

| | |
|---------------------------------------------------------------------|-------|
| Electrical durability at nominal load in AC1 in operating cycles | 50000 |
|---------------------------------------------------------------------|-------|

Voltage

Rated operational voltage U_e

230 - 240 V