



EHN011



## Daily time switch 1 channel, 1 module with reserve

### Technical properties

#### Architecture

Fixing mode	Din-Rail
-------------	----------

#### Functions

Number of function channels	1
Switching cycles	min. 50000
Power reserve	≈ 120 h

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Rated operational voltage $U_e$	230 / 240 V
Frequency	50/60 Hz

#### Electric current

Max. power with $\cos \phi$ 0.6	3 A
Switching current at $\cos \phi = 0.6$	max. 3 A

#### Dimensions

Depth of installed product	60 mm
Height of installed product	90 mm
Width of installed product	18 mm
Width of rail mounted device (RMD)	1 modules

#### Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Loss power at full load	≈ 1 W
Power dissipation per coil	0.5 W

#### Battery

Charging time of the power reserve in hours	120
---	-----

#### Fluorescent bulbs control

Compact fluorescent lamps	max. 100 W
---------------------------	------------

#### Incandescent bulbs control

Max. power with incandescent lamps	900 W
------------------------------------	-------

230 V incandescent lamps and halogen lamps

max. 900 W

### Installation, mounting

Mounting type	din-Rail
Installation mode	for mounting on DIN rail

### Connection

Connection cross-sect. flexible conductor	1 / 4mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 4mm <sup>2</sup>
Conductor cross-section (flexible)	1...4 mm <sup>2</sup>
Conductor cross-section (rigid)	1...4 mm <sup>2</sup>
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals
Type of connection	with screw

### Settings

Number of program steps	96
Summer / Winter time change	manual
Shortest switching time	15 mn
Type of programming	analog
Program cycles	Programme cycle: 24 hours
Programming cycle	24H

### Equipment

Number of channels	1
Number of switching times for on/off	96
Supply failure reserve	120 h
Switching cycles at cos φ = 0,6	min. 20000

### Use

Cycle	daily
-------	-------

### Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No

### Use conditions

Operating temperature	-10...55 °C
Working accuracy	1
Storage/transport temperature	-10...55 °C