



ERC125

Override Contactor 25A, 1NO, 230V~50Hz

Technical properties

Connection

Type of contacts	1NO
Number of contacts	1
Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1 - 10 mm ²

Electric current

Rated current	25 A
---------------	------

Capacity

Number of modules	1
-------------------	---

Frequency

Frequency	50 - 50 Hz
-----------	------------

Voltage

Rated impulse withstand voltage U _{imp}	4000 V
Rated insulation voltage U _i	250 V
Command voltage AC	230 - 230 V
Command voltage DC	0 - 0 V

Use conditions

Operating temperature	-10 - 50 °C
Storage/transport temperature	-40 - 80 °C

Endurance

Number of mechanical operations	100000
Electric endurance in number of cycles	30000

Power

Total power loss under IN	2,50 W
Inrush power absorbed	10,70 VA

Dimensions

Height	83 mm
Width	17,85 mm
Depth	60 mm

Equipment

Number of NO contacts	1
Number of NC contacts	0

Installation, mounting

Nominal tightening torque

1,20 - 1,20 Nm