



ERC225

Override Contactor 25A, 2NO, 230V~50Hz

Technical properties

Architecture

Type of order	Relay
---------------	-------

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage U_e	230 V
---------------------------------	-------

Frequency	50 Hz
-----------	-------

Voltage

Rated insulation voltage	250 V
--------------------------	-------

DC control voltage	0 V
--------------------	-----

Command voltage AC	230 V
--------------------	-------

Rated impulse withstand voltage	4 kV
---------------------------------	------

Electric current

Rated current	25 A
---------------	------

Thermal rated current outside of housings	25 A
---	------

Acceptable current load with AC7 category A	25 A
---	------

Acceptable current load with AC7 category B	8.5 A
---	-------

Dimensions

Depth of installed product	60 mm
----------------------------	-------

Height of installed product	83 mm
-----------------------------	-------

Width of installed product	17.85 mm
----------------------------	----------

Power

Inrush power absorbed	10.7 VA
-----------------------	---------

Operating consumption	2.9 VA
-----------------------	--------

Total power loss under IN	4 W
---------------------------	-----

Power loss per contact	1.5 W
------------------------	-------

Power dissipation per coil	1 W
----------------------------	-----

Contact rating with 230 V in AC7 category A	4.6 kW
---	--------

Contact rating with 230 V in AC7 category B	880 W
---	-------

Tripping

Time of response when opening	15 ms
-------------------------------	-------

Time of response when closing	25 ms
-------------------------------	-------

Endurance

Electric endurance in number of cycles	30000
Number of mechanical operations	100000

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	810 VA
Fluorescent lamps in duo circuit	1990 VA
Max. load fluorescent lamp	950 VA

Incandescent bulbs control

Max. power with incandescent lamps	1900 W
------------------------------------	--------

Installation, mounting

Tightening torque	1,2Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1 / 10mm ²
Type of contacts	2NO
Type of connection	with screw
Connection cross-section of the control cable solid	1 / 10 mm ²

Equipment

Can be accessorized	Yes
---------------------	-----

Use

Local operation/hand operation	Yes
--------------------------------	-----

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-10...50 °C
Storage/transport temperature	-40...80 °C