



ESC080

Auxiliary contact 6A, 1NO+1NC

Technical properties

Configuration

Number of modules	0.5
-------------------	-----

Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

Voltage

Rated insulation voltage	240 V
Rated impulse withstand voltage	4 kV

Electric current

Acceptable current rating with AC1	6 A
Rated current	6 A

Dimensions

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	11 mm

Power

Total power loss under IN	0.1 W
---------------------------	-------

Endurance

Electric endurance in number of cycles	30000
Number of mechanical operations	1000000

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1 / 6mm ²
Number of contacts	2
Type of contacts	1NC+1NO
Connection cross-section of the control cable solid	1 / 10 mm ²

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes

Halogen free	Yes
--------------	-----

Use conditions

Operating temperature	-10...50 °C
Storage/transport temperature	-40...80 °C