




EZN002



Delay off Timer

Technical properties

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

Power consumption during operation	15 VA
Power loss at full load	2 W
230 V incandescent and halogen lamp	450 W

Use conditions

Operating temperature	-10 - 50 °C
-----------------------	-------------

Connection

Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1.5 - 10 mm ²

Capacity

Number of modules	1
-------------------	---

Texts

Switch mode	Change-over contact, usable as NC or NO
Function	Functions: On delay, off delay, single shot leading edge/single shot trailing edge, pulse shaping, flashing symmetrically, contact open/closed
Type of connection	With screw terminals
Installation mode	For mounting on DIN rail

Dimensions

Height	85 mm
Width	17,50 mm
Depth	58 mm