



EZL100



Emergency light tester time relay 230V AC

Technical properties

Frequency

Frequency	50 - 60 Hz
-----------	------------

Use conditions

Operating temperature	-25 - 55 °C
-----------------------	-------------

Connection

Cross-section flexible conductor	0.5 - 2.5 mm ²
----------------------------------	---------------------------

Cross-section rigid conductor	0.5 - 2.5 mm ²
-------------------------------	---------------------------

Capacity

Number of modules	1
-------------------	---

Dimensions

Height	87 mm
--------	-------

Width	17,50 mm
-------	----------

Depth	65 mm
-------	-------