




EZN005



## Symmetrical Flasher

### Technical properties

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Power

Power consumption during operation	15 VA
Power loss at full load	2 W
230 V incandescent and halogen lamp	450 W

#### Use conditions

Operating temperature	-20 - 50 °C
-----------------------	-------------

#### Connection

Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 10 mm <sup>2</sup>

#### Capacity

Number of modules	1
-------------------	---

#### Texts

Switch mode	Change-over contact, usable as NC or NO
Function	Functions: On delay, off delay, single shot leading edge/single shot trailing edge, pulse shaping, flashing symmetrically, contact open/closed
Type of connection	With screw terminals
Installation mode	For mounting on DIN rail

#### Dimensions

Height	85 mm
Width	17,50 mm
Depth	58 mm