



HA306

## Load break switch 3P 125A

### Technical properties

#### Electric current

Rated current	125 A
---------------	-------

#### Connection

Cross-section rigid conductor	50 mm <sup>2</sup> max.
-------------------------------	-------------------------

#### Voltage

Rated insulation voltage $U_i$	800 V
--------------------------------	-------

Rated impulse withstand voltage $U_{imp}$	8000 V
---	--------

#### Power

Power loss per pole at $I_n$	5,70 W
------------------------------	--------

Total power loss under $I_N$	17,10 W
------------------------------	---------

Rated operational power under 400 V AC AC1	82000 W
---	---------

#### Equipment

Motor drive optional	No
----------------------	----

#### Use conditions

Operating temperature	-20 - 70 °C
-----------------------	-------------

#### Cover, door

Interlockable	Yes
---------------	-----

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Architecture

Type of pole	3P
--------------	----

Control/operation element	Short thumb grip
---------------------------	------------------