



HA304

Load break switch 3P 80A

Technical properties

Electric current

Rated current 80 A

Connection

Cross-section rigid conductor 50 mm² max.

Voltage

Rated insulation voltage U_i 800 V

Rated impulse withstand voltage U_{imp} 8000 V

Power

Power loss per pole at I_n 2 W

Total power loss under I_n 6,10 W

Rated operational power under 400 V AC
AC1 52000 W

Equipment

Motor drive optional No

Use conditions

Operating temperature -20 - 70 °C

Cover, door

Interlockable Yes

Safety

Ingress Protection (IP) class IP20

Architecture

Type of pole 3P

Control/operation element Short thumb grip