

HA307

Load break switch 3P 160A

Technical properties

Electric current

Rated current 160 A

Connection

Cross-section rigid conductor 95 mm²

Voltage

Rated insulation voltage U_i 800 V

Rated impulse withstand voltage U_{imp} 8000 V

Power

Power loss per pole at I_n 3,30 W

Total power loss under I_N 9,90 W

Rated operational power under 400 V AC
AC1 105000 W

Equipment

Motor drive optional No

Use conditions

Operating temperature -20 - 70 °C

Cover, door

Interlockable Yes

Safety

Ingress Protection (IP) class IP00

Architecture

Type of pole 3P

Control/operation element Short thumb grip