



HA457

## Load break switch 4P 400A

### Technical properties

#### Electric current

Rated current	400 A
Rated short-time withstand current I <sub>cw</sub> IEC 60947	9 kA
Acceptable current rating AC21	400 A
Acceptable current rating AC21 category A	400 A
Acceptable current rating AC21 category B	400 A
Acceptable current rating AC22 category A	400 A
Acceptable current rating AC22 category B	400 A
Acceptable current rating AC23 category A	400 A
Acceptable current rating AC23 category B	400 A
Rated short-circuit making capacity I <sub>cm</sub> under 415 V AC according to IEC 60947-3	15,30 kA
Rated short-time withstand current I <sub>cw</sub> 1s IEC 60947	9 kA

#### Architecture

Number of poles	4
Control/operation element	Long rotary handle
Device construction type	Fixed built-in
Type of pole	4P

#### Dimensions

Height	160 mm
Width	130 mm
Depth	230 mm

#### Cover, door

Interlockable	Yes
---------------	-----

#### Safety

Ingress Protection (IP) class	IP00
-------------------------------	------

#### Connection

Cross-section rigid conductor	240 mm <sup>2</sup>
Cross-section flexible conductor	240 mm <sup>2</sup>

#### Voltage

Rated insulation voltage U <sub>i</sub>	1000 V
Rated impulse withstand voltage U <sub>imp</sub>	8000 V
Rated operational voltage U <sub>e</sub>	380 - 415 V

**Power**

Power loss per pole at In	14,40 W
Total power loss under IN	57,60 W
Rated operational power under 400 V AC AC1	263000 W
Rated operational power under 400 V AC AC23	112000 W

**Controls and indicators**

Motor drive integrated	No
------------------------	----

**Use conditions**

Operating temperature	-20 - 70 °C
-----------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Functions**

Is reversing switch	No
Version as emergency stop installation	No
Version as main switch	Yes
Version as maintenance/service switch	Yes
Version as safety switch	Yes
Version as switch disconnecter compact	Yes

**Equipment**

Motor drive optional	No
Number of auxiliary contacts as change- over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

**Installation, mounting**

Nominal tightening torque	20 - 22 Nm
---------------------------	------------