



HEE801H

## Moulded Case Circuit Breaker h1000 4P 70kA 800A LSI

### Technical properties

#### Architecture

Type of order	Toggle
Number of poles	4 P
Type of pole	4P4D N:0/50/100%

#### Functions

Complete device with protection unit	Yes
Trip Unit	LSI
Integrated earth fault protection	No

#### Configuration

Number of modules	16
-------------------	----

#### Main electrical features

Rated operational voltage Ue	220 / 690 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

#### Electric current

Rated current	800 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	20 kA
Thermal protection nob setting xIN	0.4 / 0.5 / 0.63 / 0.9 / 0.95 / 1
Thermal setting current on neutral pole	0 / 0.5 / 1 In
Breaking capacity on 1 pole for IT 230V NF 60947-2	60 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	9 kA
Rated service breaking capacity Ics AC according IEC 60947-2	71 %
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	70 kA

### Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1

### Power

Total power loss under I <sub>N</sub>	153.6 W
Power loss per pole at I <sub>N</sub>	51.2 W

### Tripping

Trip mode	LSI
Thermal protection trip time	5 / 10 / 11 / 19 / 21 / 29 ms
Time of response when opening	10 ms

### Electrical specifications

Magnetic trip delay time	100 to 200 ms
--------------------------	---------------

### Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

### Installation, mounting

DIN rail mounting with optional adaptor	No
---	----

### Connection

Connection cross-sect. flexible conductor	2x240mm <sup>2</sup>
Connection cross-sect. rigid cable	2x240mm <sup>2</sup>
Connection	Front connection
Type of connection	Terminal

### Settings

Range of the magnetic adjustment	4480 / 5600 / 7000 / 8960 / 9600 / 9600 / 9600 A
Magnetic protection nob setting xI <sub>N</sub>	2.5 / 5 / 10
Setting type I <sub>N</sub> or I <sub>th</sub>	I <sub>r</sub> I <sub>th</sub>

### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	Yes

### Use cases

Category of use	A
-----------------	---

**Standards**

Standard text

IEC 60947-2

**Use conditions**

Operating temperature

-25...70 °C

Altitude

2000 m

Air humidity protection

for all climates

Storage/transport temperature

-35...70 °C