



HEF981H

## Moulded Case Circuit Breaker h1600 4P 70kA 1250A LSI

### Technical properties

#### Architecture

|                 |                  |
|-----------------|------------------|
| Type of order   | Toggle           |
| Number of poles | 4 P              |
| Type of pole    | 4P4D N:0/50/100% |

#### Functions

|                                      |     |
|--------------------------------------|-----|
| Complete device with protection unit | Yes |
| Trip Unit                            | LSI |
| Integrated earth fault protection    | No  |

#### Configuration

|                   |    |
|-------------------|----|
| Number of modules | 16 |
|-------------------|----|

#### Main electrical features

|                              |             |
|------------------------------|-------------|
| Rated operational voltage Ue | 220 / 690 V |
| Frequency                    | 50/60 Hz    |

#### Voltage

|                                 |       |
|---------------------------------|-------|
| Rated insulation voltage        | 800 V |
| Rated impulse withstand voltage | 8 kV  |
| With under voltage release      | No    |

#### Electric current

|  |   |
|--|---|
| Rated current  | 1250 A                                  |
| Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2 | 45 kA                                   |
| Thermal protection nob setting xIN   | 0.4 / 0.5 / 0.63 / 0.8 / 0.9 / 0.95 / 1 |
| Thermal setting current on neutral pole                                      | 0 / 0.5 / 1 In                          |
| Breaking capacity on 1 pole for IT 230V NF 60947-2                           | 60 kA                                   |
| Breaking capacity on 1 pole for IT 400V NF 60947-2                           | 9 kA                                    |
| Rated service breaking capacity Ics AC according IEC 60947-2                 | 71 %                                    |
| Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2 | 100 kA                                  |
| Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2 | 100 kA                                  |
| Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2 | 70 kA                                   |
| Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2 | 70 kA                                   |

### Current correction factors

|   |   |
|---|---|
| Correction factor of rating current for 2 devices placed side-by-side       | 1 |
| Correction factor of rating current for 3 devices placed side-by-side       | 1 |
| Correction factor of rating current for 4 and 5 devices placed side-by-side | 1 |
| Correction factor of rating current for 6 devices placed side-by-side       | 1 |

### Power

|                           |         |
|---------------------------|---------|
| Total power loss under IN | 187.5 W |
| Power loss per pole at In | 62.5 W  |

### Tripping

|                               |                               |
|-------------------------------|-------------------------------|
| Tripmode                      | LSI                           |
| Thermal protection trip time  | 5 / 10 / 11 / 19 / 21 / 29 ms |
| Time of response when opening | 10 ms                         |

### Electrical specifications

|                          |               |
|--------------------------|---------------|
| Magnetic trip delay time | 100 to 200 ms |
|--------------------------|---------------|

### Endurance

|  |      |
|--|------|
| Electric endurance in number of cycles | 1000 |
| Number of mechanical operations        | 4000 |

### Installation, mounting

|   |    |
|---|----|
| DIN rail mounting with optional adaptor | No |
|---|----|

### Connection

|   |                      |
|---|----------------------|
| Connection cross-sect. flexible conductor | 3x240mm <sup>2</sup> |
| Connection cross-sect. rigid cable        | 3x240mm <sup>2</sup> |
| Connection                                | Front connection     |
| Type of connection                        | Terminal             |

### Settings

|                                     |   |
|-------------------------------------|---|
| Range of the magnetic adjustment    | 7000 / 8750 / 11200 / 14000 / 15000 / 15000 / 15000 A |
| Magnetic protection nob setting xIN | 2.5 / 5 / 10  |
| Setting type In or Ith              | IrTh  |

### Equipment

|   |     |
|---|-----|
| Number of auxiliary contacts as normally closed contact | 0   |
| Number of auxiliary contacts as normally open contact   | 0   |
| Number of auxiliary contacts as change-over contact     | 0   |
| Motor drive optional                                    | Yes |

### Use cases

**Standards**

---

|               |             |
|---------------|-------------|
| Standard text | IEC 60947-2 |
|---------------|-------------|

**Use conditions**

---

|                       |             |
|-----------------------|-------------|
| Operating temperature | -25...70 °C |
|-----------------------|-------------|

---

|          |        |
|----------|--------|
| Altitude | 2000 m |
|----------|--------|

---

|                         |                  |
|-------------------------|------------------|
| Air humidity protection | for all climates |
|-------------------------|------------------|

---

|                               |             |
|-------------------------------|-------------|
| Storage/transport temperature | -35...70 °C |
|-------------------------------|-------------|