



HEC041H

Moulded Case Circuit Breaker h250 4P 70kA 40A LSI

Technical properties

Architecture

| | |
|-----------------|------------------|
| Type of order | Toggle |
| Number of poles | 4 P |
| Type of pole | 4P4D N:0/50/100% |

Functions

| | |
|--------------------------------------|-----|
| Complete device with protection unit | Yes |
| Trip Unit | LSI |
| Integrated earth fault protection | No |

Configuration

| | |
|-------------------|---|
| Number of modules | 8 |
|-------------------|---|

Main electrical features

| | |
|------------------------------|-------------|
| Rated operational voltage Ue | 220 / 690 V |
| Frequency | 50/60 Hz |

Voltage

| | |
|---------------------------------|-------|
| Rated insulation voltage | 800 V |
| Rated impulse withstand voltage | 8 kV |
| With under voltage release | No |

Electric current

| | |
|------------------------------------------------------------------------------|-----------------------------------------|
| Rated current | 40 A |
| Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2 | 20 kA |
| Thermal protection nob setting xIN | 0.4 / 0.5 / 0.63 / 0.8 / 0.9 / 0.95 / 1 |
| Thermal setting current on neutral pole | 0 / 0.5 / 1 In |
| Breaking capacity on 1 pole for IT 230V NF 60947-2 | 51 kA |
| Breaking capacity on 1 pole for IT 400V NF 60947-2 | 9 kA |
| Rated service breaking capacity Ics AC according IEC 60947-2 | 71 % |
| Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2 | 100 kA |
| Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2 | 85 kA |
| Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2 | 70 kA |
| Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2 | 70 kA |

Current correction factors

| | |
|-----------------------------------------------------------------------------|---|
| Correction factor of rating current for 2 devices placed side-by-side | 1 |
| Correction factor of rating current for 3 devices placed side-by-side | 1 |
| Correction factor of rating current for 4 and 5 devices placed side-by-side | 1 |
| Correction factor of rating current for 6 devices placed side-by-side | 1 |

Power

| | |
|---------------------------|-------|
| Total power loss under IN | 1.9 W |
| Power loss per pole at In | 0.6 W |

Tripping

| | |
|-------------------------------|--------------------|
| Tripmode | LSI |
| Thermal protection trip time | 5 / 8 / 11 / 21 ms |
| Time of response when opening | 10 ms |

Electrical specifications

| | |
|--------------------------|---------------|
| Magnetic trip delay time | 100 to 200 ms |
|--------------------------|---------------|

Endurance

| | |
|----------------------------------------|------|
| Electric endurance in number of cycles | 1000 |
| Number of mechanical operations | 4000 |

Installation, mounting

| | |
|-----------------------------------------|----|
| DIN rail mounting with optional adaptor | No |
|-----------------------------------------|----|

Connection

| | |
|-------------------------------------------|-------------------------|
| Connection cross-sect. flexible conductor | 35 / 150mm ² |
| Connection cross-sect. rigid cable | 35 / 185mm ² |
| Connection | Front connection |
| Type of connection | Terminal |

Settings

| | |
|-------------------------------------|-------------------------------------------|
| Range of the magnetic adjustment | 224 / 280 / 350 / 448 / 504 / 532 / 560 A |
| Magnetic protection nob setting xIN | 2.5 / 5 / 10 |
| Setting type In or Ith | IrTh |

Equipment

| | |
|---------------------------------------------------------|-----|
| Number of auxiliary contacts as normally closed contact | 0 |
| Number of auxiliary contacts as normally open contact | 0 |
| Number of auxiliary contacts as change-over contact | 0 |
| Motor drive optional | Yes |

Use cases

| | |
|-----------------|---|
| Category of use | A |
|-----------------|---|

Standards

Standard text

IEC 60947-2

Use conditions

Operating temperature

-25...70 °C

Altitude

2000 m

Air humidity protection

for all climates

Storage/transport temperature

-35...70 °C