



HEC125H

## Moulded Case Circuit Breaker h250 3P 70kA 125A LSI

### Technical properties

#### Electric current

Rated current	125 A
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400 V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 240 V AC IEC 60947-2	85 kA

#### Architecture

Number of poles	3
-----------------	---

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Voltage

Rated impulse withstand voltage U <sub>imp</sub>	8000 V
Rated insulation voltage U <sub>i</sub>	800 V

#### Functions

Trip unit	LSI
-----------	-----

#### Main electrical attributes

Magnetic protection trip time	100 - 200 ms
-------------------------------	--------------

#### Power

Total power loss under I <sub>N</sub>	18,30 W
---------------------------------------	---------

#### Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

#### Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

#### Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

#### Connection

Cross-section flexible conductor	35 - 150 mm <sup>2</sup>
Cross-section rigid conductor	35 - 185 mm <sup>2</sup>
Connector/plug type	Terminal

#### Installation, mounting

Nominal tightening torque	12 - 12 Nm
---------------------------	------------

**Settings**

---

Adjustment range short-term delayed short-circuit release

0 - 0 A