



HHA030Z

Moulded Case Circuit Breaker h3 x160 TM FIX 1P1D 32A 25kA CTC

Technical properties

Architecture

| | |
|---------------------------|-----------------|
| Neutral position | without neutral |
| Number of protected poles | 1 |
| Number of poles | 1 P |

Functions

| | |
|-----------------------------------|--------|
| Trip Unit | TM F/F |
| Integrated earth fault protection | No |
| Concurrently switching N-neutral | No |

Controls and indicators

| | |
|------------------------|----|
| Motor drive integrated | No |
|------------------------|----|

Main electrical features

| | |
|------------------------------|-------------|
| Rated operational voltage Ue | 220 / 240 V |
| Type of supply voltage | AC |
| Frequency | 50/60 Hz |

Voltage

| | |
|---------------------------------|-------|
| Rated insulation voltage | 690 V |
| Rated impulse withstand voltage | 8 kV |
| With under voltage release | No |

Electric current

| | |
|--|--------|
| Rated current | 32 A |
| Thermal protection nob setting xIN | 1 |
| Rating current 10°C according to IEC 60947 | 43.8 A |
| Rating current 15°C according to IEC 60947 | 42.5 A |
| Rating current 20°C according to IEC 60947 | 41.2 A |
| Rating current 25°C according to IEC 60947 | 39.8 A |
| Rating current 30°C according to IEC 60947 | 38.4 A |
| Rating current 35°C according to IEC 60947 | 36.9 A |
| Rating current 40°C according to IEC 60947 | 35.3 A |
| Rating current 45°C according to IEC 60947 | 33.7 A |
| Rating current 50°C according to IEC 60947 | 32 A |
| Rating current 55°C according to IEC 60947 | 30.1 A |
| Rating current 60°C according to IEC 60947 | 28.2 A |
| Rating current 65°C according to IEC 60947 | 26.1 A |
| Rating current 70°C according to IEC 60947 | 23.9 A |

| | |
|--|-------|
| Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2 | 35 kA |
| Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2 | 35 kA |
| Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2 | 25 kA |
| Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2 | 25 kA |
| Range of the thermal adjustment | 32 A |
| Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2 | 25 kA |

Dimensions

| | |
|-----------------------------|--------|
| Depth of installed product | 68 mm |
| Height of installed product | 130 mm |
| Width of installed product | 25 mm |

Frequency

| | |
|-----------|-------------|
| Frequency | 50 to 60 Hz |
|-----------|-------------|

Power

| | |
|---------------------------|-----|
| Total power loss under IN | 3 W |
| Power loss per pole at In | 3 W |

Endurance

| | |
|--|------|
| Electric endurance in number of cycles | 1000 |
| Number of mechanical operations | 4000 |

Installation, mounting

| | |
|-------------------|-----|
| Tightening torque | 6Nm |
|-------------------|-----|

Connection

| | |
|------------------------------------|-----------------------|
| Connection cross-sect. rigid cable | 6 / 95mm ² |
| Type of connection | with screw |

Cable

| | |
|----------------|----|
| Cable Material | Cu |
|----------------|----|

Settings

| | |
|----------------------------------|-------|
| Range of the magnetic adjustment | 600 A |
|----------------------------------|-------|

Equipment

| | |
|---|-----|
| Number of auxiliary contacts as normally closed contact | 0 |
| Number of auxiliary contacts as normally open contact | 0 |
| Number of auxiliary contacts as change-over contact | 0 |
| Can be accessorized | Yes |

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|--|--------|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | No |
| Use conditions | |
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3 |
| Altitude | 2000 m |
| temperatur | |
| Temperature of calibration | 50 °C |