



HI456



## Change-over switch 4P 400A

### Technical properties

#### Architecture

Number of poles	4 P
Type of pole	4 P
Type of case	Fixed built-in

#### Functions

Reversing switch	Yes
Version as main switch	Yes
Version as emergency stop installation	No
Version as safety switch	Yes
Version as maintenance-/service switch	Yes

#### Controls and indicators

Motor drive integrated	No
------------------------	----

#### Main electrical features

Rated operational voltage Ue	380 / 415 / 500 / 690 V
------------------------------	-------------------------

#### Voltage

Rated insulation voltage	1000 V
Rated impulse withstand voltage	12 kV
Rated operational voltage in DC	220 / 440 V

#### Electric current

Rated operational current in AC21category B	400 A
Acceptable current rating with AC22 category A	400 A
Rated current	400 A
Short-circuit current with gI-gG fuses	50 kA
Making capacity in peak short circuit	22 kA
Rated short-time withstand current I <sub>cw</sub>	15 kA
Rated short-time withstand current 1s	8 kA
Rating current 10°C according to IEC 60947	400 A
Rating current 15°C according to IEC 60947	400 A
Rating current 20°C according to IEC 60947	400 A
Rating current 25°C according to IEC 60947	400 A
Rating current 30°C according to IEC 60947	400 A
Rating current 35°C according to IEC 60947	400 A
Rating current 40°C according to IEC 60947	400 A

Rating current 45°C according to IEC 60947	360 A
Rating current 5°C according to IEC 60947	400 A
Rating current 50°C according to IEC 60947	360 A
Rating current 55°C according to IEC 60947	320 A
Rating current 60°C according to IEC 60947	320 A
Rating current 65°C according to IEC 60947	280 A
Rating current 70°C according to IEC 60947	280 A
Rated operational current in AC21 category A	400 A
Acceptable current rating with AC22 category B	400 A
Rated operational current in AC23 category A	400 A
Acceptable current rating with AC23 category B	400 A
Conventional thermal current under enclosure at 40°C	400 A
<b>Dimensions</b>	
Depth of installed product	218 mm
Height of installed product	170 mm
Width of installed product	312 mm
<b>Power</b>	
Contact rating with 400 V in AC1	263 kW
<b>Cover, door</b>	
Interlockable	Yes
<b>Materials</b>	
Toggle colour	Black
<b>Installation, mounting</b>	
Suitable for front mounting center	No
Suitable for front mounting	No
Suitable for ground mounting	Yes
<b>Connection</b>	
Type of connection	Terminal
<b>Equipment</b>	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No
<b>Standards</b>	
Standard text	IEC 60947-3 ; IEC 60947-6
European directive WEEE	concerned

