



HHS025DR

**Moulded Case Circuit Breaker h3+ P160 TM ADJ 3P3D 25A 25kA FTC**

**Technical properties**

**Electric current**

Rated current	25 A
Rated ultimate short-circuit breaking capacity $I_{cu}$ under 400 V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity $I_{cu}$ under 240 V AC IEC 60947-2	35 kA
Rated service breaking capacity $I_{cs}$ under 230 V AC according to IEC 60947-2	35 kA
Rated service breaking capacity $I_{cs}$ under 400 V AC according to IEC 60947-2	25 kA

**Architecture**

Number of poles	3
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Without neutral

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Voltage**

Rated impulse withstand voltage $U_{imp}$	8000 V
Rated insulation voltage $U_i$	800 V
Rated operational voltage $U_e$	220 - 690 V

**Functions**

Trip unit	TM A/A
-----------	--------

**Power**

Total power loss under IN	19,50 W
---------------------------	---------

**Endurance**

Electric endurance in number of cycles	10000
Number of mechanical operations	40000

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------

**Connection**

Cross-section flexible conductor	6 - 70 mm <sup>2</sup>
Cross-section rigid conductor	6 - 95 mm <sup>2</sup>

**Cover, door**

Interlockable

Yes

---

**Cable**

Cable material

Copper, Aluminium

---

**Compatibility**

Compatible with RDC AOB

No

Suitable for DIN Rail

No

Suitable for distribution board

Yes

---

**Dimensions**

Height

130 mm

Width

90 mm

Depth

97 mm

---

**Installation, mounting**

Mounting-/Connection Position

Front

Nominal tightening torque

6 - 6 Nm

---

**Electrical protection**

Instantaneous protection (li): dial setting  
coefficient

6, 8, 10, 12