



HIB412M

**Motorized transfer switch 4P 125A**

**Technical properties**

**Architecture**

Number of poles	4 P
Type of pole	4 P
Type of case	Fixed built-in

**Functions**

Reversing switch	Yes
------------------	-----

**Controls and indicators**

Motor drive integrated	Yes
------------------------	-----

**Main electrical features**

Rated operational voltage Ue	380 / 415 V
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V

**Electric current**

Rated operational current in AC21category B	125 A
Acceptable current rating with AC22 category A	125 A
Rated current	125 A
Short-circuit current with gI-gG fuses	100 kA
Rated short-time withstand current 1s	7 kA
Rating current 10°C according to IEC 60947	125 A
Rating current 15°C according to IEC 60947	125 A
Rating current 20°C according to IEC 60947	125 A
Rating current 25°C according to IEC 60947	125 A
Rating current 30°C according to IEC 60947	125 A
Rating current 35°C according to IEC 60947	125 A
Rating current 40°C according to IEC 60947	125 A
Rating current 45°C according to IEC 60947	112.5 A
Rating current 5°C according to IEC 60947	125 A
Rating current 50°C according to IEC 60947	112.5 A
Rating current 55°C according to IEC 60947	100 A
Rating current 60°C according to IEC 60947	100 A
Rating current 65°C according to IEC 60947	87.5 A

Rating current 70°C according to IEC 60947	87.5 A
Rated operational current in AC21 category A	125 A
Acceptable current rating with AC22 category B	125 A
Rated operational current in AC23 category A	125 A
Acceptable current rating with AC23 category B	125 A
Conventional thermal current under enclosure at 40°C	125 A
<b>Power</b>	
Total power loss under I <sub>N</sub>	7.6 W
Power loss per pole at I <sub>n</sub>	1.9 W
Contact rating with 400 V in AC1	82 kW
<b>Cover, door</b>	
Interlockable	Yes
<b>Connection</b>	
Type of connection	Terminal
<b>Equipment</b>	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No
<b>Standards</b>	
Standard text	IEC 60947-3 ; IEC 60947-6
European directive WEEE	concerned
<b>Safety</b>	
Protection index IP	IP00
<b>Use conditions</b>	
Altitude	2000 m
Storage/transport temperature	-40...70 °C