



HIC480G

## Automatic transfer switch 4x 800A

### Technical properties

#### Voltage

Rated operational voltage  $U_e$  380 - 415 V

#### Electric current

Rated current 800 A

Rated conditional short-circuit current  $I_{cc}$   
with gI-gG fuses 50 kA

#### Power

Rated operational power under 400 V AC  
AC1 526000 W

#### Architecture

Number of poles 4

Device construction type Fixed built-in

#### Compatibility

Suitable for DIN Rail Yes

Suitable for distribution board Yes