



HMC390T

## MCB 3P 15kA C-100A 4.5M

### Technical properties

#### Architecture

Type of pole	3P
Curve	C

#### Voltage

Rated operational voltage $U_e$	400 - 415 V
Type voltage supply	AC
Rated insulation voltage $U_i$	500 V
Rated impulse withstand voltage $U_{imp}$	6000 V

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Installation, mounting

Nominal tightening torque	3,5 - 5,0 Nm
Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	Screw terminal

#### Electric current

Rated current	100 A
Rated short-circuit breaking capacity $I_{cn}$ under 230 V AC according to IEC 60898-1	15 kA
Rated ultimate short-circuit breaking capacity $I_{cu}$ under 230 V AC IEC 60947-2	15 kA
Rated ultimate short-circuit breaking capacity $I_{cu}$ under 400 V AC IEC 60947-2	15 kA
Rated current at 0°C	124 A
Rated current 5°C	120 A
Rated current 10°C	116 A
Rated current 15°C	112 A
Rated current at 20°C	108 A
Rated current 25°C	104 A
Rated current 30°C	100 A
Rated current 35°C	96,60 A
Rated current at 40°C	93,10 A
Rated current at 45°C	89,40 A
Rated current at 50°C	85,60 A
Rated current 55°C	81,60 A
Rated current 60°C	77,50 A

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	15 kA
Nominal tightening torque down terminal	3,60 - 3,60 Nm
Nominal tightening torque top terminal	3,60 - 3,60 Nm

**Power**

Total power loss under I <sub>N</sub>	21,66 W
---------------------------------------	---------

**Endurance**

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 70 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 50 mm <sup>2</sup>
Cross-section flexible conductor	50 mm <sup>2</sup>
Cross-section rigid conductor	70 mm <sup>2</sup>

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C

**Capacity**

Number of modules	4,50
-------------------	------

**Connectivity**

Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

**Dimensions**

Height	90 mm
Width	80 mm
Depth	70 mm