



HIB412M

Motorized transfer switch 4P 125A

Technical properties

Architecture

Type of order	Not applicable
Number of poles	4 P
Type of pole	4 P
Type of case	Fixed built-in

Functions

Reversing switch	Yes
------------------	-----

Controls and indicators

Motor drive integrated	Yes
------------------------	-----

Main electrical features

Rated operational voltage Ue	380 / 415 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V

Electric current

Rated operational current in AC21category B	125 A
Acceptable current rating with AC22 category A	125 A
Rated current	125 A
Short-circuit current with gI-gG fuses	100 kA
Rated short-time withstand current 1s	7 kA
Rating current 10°C according to IEC 60947	125 A
Rating current 15°C according to IEC 60947	125 A
Rating current 20°C according to IEC 60947	125 A
Rating current 25°C according to IEC 60947	125 A
Rating current 30°C according to IEC 60947	125 A
Rating current 35°C according to IEC 60947	125 A
Rating current 40°C according to IEC 60947	125 A
Rating current 45°C according to IEC 60947	112.5 A
Rating current 5°C according to IEC 60947	125 A
Rating current 50°C according to IEC 60947	112.5 A
Rating current 55°C according to IEC 60947	100 A
Rating current 60°C according to IEC 60947	100 A

Rating current 65°C according to IEC 60947	87.5 A
Rating current 70°C according to IEC 60947	87.5 A
Rated operational current in AC21 category A	125 A
Acceptable current rating with AC22 category B	125 A
Rated operational current in AC23 category A	125 A
Acceptable current rating with AC23 category B	125 A
Conventional thermal current under enclosure at 40°C	125 A
Power	
Total power loss under I _N	7.6 W
Power loss per pole at I _N	1.9 W
Contact rating with 400 V in AC1	82 kW
Cover, door	
Interlockable	Yes
Installation, mounting	
Tightening torque	9 - 9.9 Nm
Connection	
Type of connection	Terminal
Equipment	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No
Standards	
Standard text	IEC 60947-3 ; IEC 60947-6
Safety	
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Use conditions	
Altitude	2000 m
Storage/transport temperature	-40...70 °C